SQUARE D





Mini circuit breaker, Homeline, 20A, 1 pole, 120VAC, 10kA AIR, ARC fault, pigtail neutral, plug in, UL

HOM120AFI

① Discontinued

! Discontinued on: Jun 30, 2023

Product availability: Stock - Normally stocked in distribution facility

#### Main

Product	Miniature circuit-breaker	
Range	Homeline	
Current Rating	20 A	
Certifications	UL Listed	
Voltage Rating	120 V AC	
Mounting Type	Plug-in	
Number Of Poles	1P	
Short Circuit Current Rating	10 kA	
Number Of Spaces	1	
Circuit Breaker Type	ARC-fault	
Ratings	HACR rated	
Electrical Connection	Screw clamp terminals	
Wire Size	1 x AWG 14AWG 8 ( aluminium/copper )	

### Complementary

Tightening Torque	35.40 lbf.in (4.0 N.m) 0.000.01 in² (2.56 mm²) (AWG 14AWG 8)	
Height	3.13 in (79.50 mm)	
Width	1 in (25.40 mm)	
Depth	2.98 in (75.69 mm)	

### **Environment**

Ambient Air Temperature For 104 °F (40 °C)

## Ordering and shipping details

Category	US1DE3D06301
Discount Schedule	DE3D
Gtin	785901301325
Returnability	Yes
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.39 in (0.991 cm)
Package 1 Width	0.12 in (0.305 cm)
Package 1 Length	0.55 in (1.397 cm)
Package 1 Weight	1.37 lb(US) (0.621 kg)

## **Contractual warranty**

Warranty Lifetime



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Halogen Free Product	

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov