Product data sheet

Specifications



Mini circuit breaker, Homeline, 20A, 1 pole, 120VAC, 10kA AIR, ground fault class A, plug in, UL

HOM120GFI

Product availability: Stock - Normally stocked in distribution facility

Price*: 212.00 USD

Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	20 A
Certifications	UL Listed
Voltage Rating	120 V AC
Mounting Type	Plug-in
Number Of Poles	1P
Short Circuit Current Rating	10 kA
Number Of Spaces	1
Circuit Breaker Type	Ground fault protecting class A 6 mA
Ratings	HACR rated
Electrical Connection	Screw clamp terminals
Wire Size	1 x AWG 14AWG 10 (aluminium/copper)

Complementary

Tightening Torque	36.29 lbf.in (4.1 N.m) 0.000.01 in ² (2.56 mm ²) (AWG 14AWG 10)	
Height	3.13 in (79.50 mm)	
Width	1 in (25.40 mm)	
Depth	2.98 in (75.69 mm)	

Environment

Ambient Air Temperature For 104 °F (40 °C) Operation

Ordering and shipping details

Category	US1DE3D00063	
Discount Schedule	DE3D	
Gtin	785901065371	
Returnability	Yes	
Country Of Origin	MX	

Packing Units

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.78 in (7.05 cm)
Package 1 Width	0.41 in (1.03 cm)
Package 1 Length	4.35 in (11.05 cm)
Package 1 Weight	10.41 oz (295.0 g)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	38
Package 2 Height	3.95 in (10.03 cm)
Package 2 Width	13.80 in (35.05 cm)
Package 2 Length	20.48 in (52.03 cm)
Package 2 Weight	24.71 lb(US) (11.21 kg)

Contractual warranty

Warranty

Lifetime

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov