Product data sheet

Specifications

SQUARE D

Green



Load center, Homeline, 1 phase, 24 spaces, 48 circuits, 125A convertible main lugs, PoN, NEMA1, Qwik-grip, gnd bar

HOM2448L125PQGC

Product availability: Stock - Normally stocked in distribution facility

Price*: 371.52 USD

Main

Product Type	Load Center
Marketing Trade Name	Homeline
Load Center Type	PoN Convertible Mains (lugs)
Rated Current	125 A
Number Of Spaces	24
Maximum Number Of Single Pole Circuits	48
Enclosure Rating	NEMA 1 indoor
Cover Type	Combination flush/surface cover
Electrical Connection	Lugs
Provided Equipment	Grounding bar 1) Qwik grip assembly kit 1)

Complementary

Max Short Circuit Current Rating	10 kA
Maximum Number Of Tandem Breakers	24
Number Of Phases	1 phase
Voltage Rating	120/240 V AC
Wire Size	AWG 6AWG 2/0 aluminium AWG 6AWG 1 copper
Ground Bar	Grounding bar included (not installed)
Wiring Configuration	3-wire
Enclosure Material	Welded galvannealed steel
Surface Finish	Baked enamel Gray
Box Number	8Q
Bus Rated Current	125.0 A
Height	26.02 in (661 mm)
Width	14.25 in (362 mm)
Depth	3.74 in (95 mm)

Environment

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US1DE3C00045
Discount Schedule	DE3C
Gtin	785901593553
Returnability	Yes
Country Of Origin	US

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.74 in (9.5 cm)
Package 1 Width	14.25 in (36.2 cm)
Package 1 Length	26.02 in (66.1 cm)
Package 1 Weight	24.41 lb(US) (11.072 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	18
Package 2 Height	39.50 in (100.33 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	469.00 lb(US) (212.735 kg)

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov