Product data sheet

Specifications

Safety switch, light duty, fusible, 30A, 2 wire, 1 pole, 1 neutral, 120VAC, Type 1

L111N

Product availability: Stock - Normally stocked in distribution facility

Price*: 54.00 USD

Main

Product	Single Throw Safety Switch	
Duty Rating	Light duty	
Device Application	Furnace Garages	
Disconnect Type	Fusible disconnect	
Factory Installed Neutral	Neutral (factory installed)	
Phase	3 phase	
Number Of Poles	1	
Current Rating	Rating 30 A	
Voltage Rating	120 V AC	
Nema Degree Of Protection	NEMA 1	

Complementary

•	
Short-Circuit Current	10 kA
Fuse Type	Plug
Mounting Type	Surface
Wiring Configuration	2-wire
Wire Size	AWG 14AWG 8 copper AWG 12AWG 8 aluminium
Tightening Torque	30 lbf.in (3.39 N.m) 0.000.01 in ² (2.0828.367 mm ²) (AWG 14AWG 8) 30 lbf.in (3.39 N.m) 0.010.01 in ² (3.3078.367 mm ²) (AWG 12AWG 8)
Depth	4 in (101.60 mm)
Width	6.13 in (155.70 mm)
Height	7.63 in (193.80 mm)

Ordering and shipping details

Category	US1DE1A00057
Discount Schedule	DE1A
Gtin	785901115489
Returnability	Yes
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.50 in (13.97 cm)
Package 1 Width	6.40 in (16.256 cm)
Package 1 Length	8.60 in (21.844 cm)
Package 1 Weight	3.28 lb(US) (1.488 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	200
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	678.00 lb(US) (307.535 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

REACh Declaration
Compliant
EU RoHS Declaration
China RoHS declaration
Pro-active China RoHS declaration (out of China RoHS legal scope)
Product Environmental Profile
No need of specific recycling operations
WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov