





Circuit breaker, LA, unit mount, 125A, 3 pole, 600VAC, shunt trip

LAL361251021

Discontinued on: Jul 10, 2021

(!) Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| Product Or Component Type | Circuit breaker |
|---------------------------|------------------|
| Trip Unit Technology | Thermal-magnetic |

Complementary

| Line Rated Current | 125 A | |
|-----------------------------|---|--|
| Number Of Poles | 3P | |
| Mounting Mode | Unit mount | |
| Magnetic Hold Current | 625 A | |
| Magnetic Tripping Current | 1250 A | |
| Electrical Connection | Lugs, load Lugs, line | |
| Terminal Identifier | AL400LA | |
| Tightening Torque | 115.06 lbf.in (13 N.m) 0.070.47 in² (42304 mm²) (AWG 1600 kcmil) 115.06 lbf.in (13 N.m) 0.070.20 in² (42127 mm²) (AWG 1250 kcmil) | |
| Height | 11 in (279.40 mm) | |
| Width | 6 in (152.40 mm) | |
| Depth | 5.84 in (148.34 mm) | |
| Circuit Breaker Application | it Breaker Application HACR rated | |

Environment

| Certifications | III I interd | |
|----------------|--------------|--|
| Certifications | UL Listed | |
| | CSA | |
| | | |
| | IEC | |

Ordering and shipping details

| Category | US10DE200935 |
|-------------------|--------------|
| Discount Schedule | 0DE2 |
| Gtin | 785901915843 |
| Returnability | No |
| Country Of Origin | US |

Packing Units

Unit Type Of Package 1 PCE

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Number Of Units In Package 1 | 1 |
|------------------------------|-------------------------|
| Package 1 Height | 8.44 in (21.433 cm) |
| Package 1 Width | 11.13 in (28.258 cm) |
| Package 1 Length | 17.13 in (43.498 cm) |
| Package 1 Weight | 16.77 lb(US) (7.605 kg) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| Ø | Mercury Free |
|----------|------------------------------------|
| ⊘ | Rohs Exemption Information Yes |
| ⊘ | Pvc Free |
| ⊘ | Halogen Free Plastic Parts Product |

Certifications & Standards

| Eu Rohs Directive | Compliant |
|---------------------------|--|
| | EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |