## Product data sheet

Specifications





# Suppressor module, TeSys Deca, varistor, 24 to 48VAC

LAD4VE

Product availability: Stock - Normally stocked in distribution facility

#### Price\*: 31.44 USD

#### Main

Range	TeSys
Device Short Name	LAD4
Product Or Component Type	Suppressor module
Product Compatibility	3P LC1D09D38 4P LC1DT20DT40 4P LC1D098D258 CAD32, CAD50

## Complementary

25
or (peak limiting)
B V AC

### Environment

Standards	IEC 60947-5-1 EN 60947-5-1 CSA C22.2 No 60947-5-1 UL 60947-5-1 GB/T 14048.5
Product Certifications	UL CSA
Ip Degree Of Protection	IP2XIEC 60529
Ambient Air Temperature For Operation	-13131 °F (-2555 °C)
Ambient Air Temperature For Storage	-40176 °F (-4080 °C)

## Ordering and shipping details

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Category	US10I1222341	
Discount Schedule	0112	
Gtin	3389110385496	
Returnability	Yes	
Country Of Origin	US	

## **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.43 in (1.100 cm)
Package 1 Width	3.94 in (10.000 cm)
Package 1 Length	1.97 in (5.000 cm)
Package 1 Weight	0.48 oz (13.700 g)
Unit Type Of Package 2	S01
Number Of Units In Package 2	70
Package 2 Height	5.91 in (15 cm)
Package 2 Width	5.91 in (15 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	2.58 lb(US) (1.169 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	1120
Package 3 Height	17.72 in (45.000 cm)
Package 3 Width	23.62 in (60.000 cm)
Package 3 Length	31.50 in (80.000 cm)
Package 3 Weight	85.94 lb(US) (38.980 kg)

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

## **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations