

Product data sheet

Specifications



Circuit breaker, LA, 400A, 2 pole, 600VAC, 22kA, 250VDC, unit mount, thermal magnetic, short handle

LAP26400MB

Product availability: Stock - Normally stocked in distribution facility

Price*: 3,807.00 USD

Main

Product Or Component Type	Circuit breaker
Trip Unit Technology	Magnetic

Complementary

Line Rated Current	400 A
Number Of Poles	2P
Breaking Capacity Code	A
Mounting Mode	Unit mount
Wiring Configuration	3-wire
Magnetic Hold Current	2000 A
Magnetic Tripping Current	4000 A
Operator	Short lever
Electrical Connection	Lugs, load Terminal, line
Terminal Identifier	AL400LA
Height	11 in (279.40 mm)
Width	6 in (152.40 mm)
Depth	5.84 in (148.34 mm)
Circuit Breaker Application	HACR rated

Environment

Certifications	UL Listed IEC CSA
----------------	-------------------------

Ordering and shipping details

Category	US10DE200935
Discount Schedule	0DE2
Gtin	785901530022
Returnability	No
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.21 in (23.4 cm)
Package 1 Width	11.50 in (29.2 cm)
Package 1 Length	17.28 in (43.9 cm)
Package 1 Weight	14.07 lb(US) (6.38 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.





[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
 Pvc Free	
 Halogen Free Plastic Parts Product	

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov