

# Product data sheet

Specifications



## Full Voltage Non-Reversing Starter TeSys D, 3 pole, Type 1, 9A, 480VAC Coil

LE1D093A62OT70

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 164.00 USD

### Main

Product Or Component Type	Full voltage starter
Range Of Product	Instakits
Starter Type	Non reversing

### Complementary

Control Circuit Voltage	480 V AC 50/60 Hz
Current Rating	20 A AC-1 9 A AC-3
Horsepower Rating	1 hp 240 V AC, 1 phase 2 hp 208 V AC, 3 phase 2 hp 230 V AC, 3 phase 5 hp 460 V AC, 3 phase 7.5 hp 575 V AC, 3 phase 0.33 hp 120 V AC, 1 phase
Maximum Voltage Rating	600 V AC
Auxiliary Contacts	1 NO + 1 NC
Location Of Connection	Line
Height	10.04 in (255 mm)
Depth	7.01 in (178 mm)
Width	6.77 in (172 mm)

### Environment

Product Certifications	CSA IEC UL
Enclosure Type	NEMA 1 painted sheet steel

### Ordering and shipping details

Category	US10I1122313
Discount Schedule	0I11
Gtin	785901756859
Returnability	Yes
Country Of Origin	MX

### Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.29 in (23.6 cm)
Package 1 Width	10.59 in (26.9 cm)
Package 1 Length	14.61 in (37.1 cm)
Package 1 Weight	10.12 lb(US) (4.59 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Pvc Free	

Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to <a href="#">www.P65Warnings.ca.gov</a>