





# Circuit breaker, LH, 200A, 3 pole, 600VAC, 25kA, 250VDC, 50kA, busbar

LHF36200

! Discontinued on: Nov 20, 2023



Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Product Or Component Type	Circuit breaker
Trip Unit Technology	Thermal-magnetic

#### Complementary

Line Rated Current	200 A	
Number Of Poles	3P	
Breaking Capacity Code	н	
Mounting Mode	Unit mount	
Magnetic Hold Current	2000 A	
Magnetic Tripping Current	4000 A	
Electrical Connection	Busbar connection, line Busbar connection, load	
Tightening Torque	Torque 115.06 lbf.in (13 N.m) 0.070.47 in² (42304 mm²) (AWG 1600 kcmil) 115.06 lbf.in (13 N.m) 0.070.20 in² (42127 mm²) (AWG 1250 kcmil)	
Height	12.5 in (317.50 mm)	
Width	6 in (152.40 mm)	
Depth	4 in (101.60 mm)	
Circuit Breaker Application	HACR rated	

#### **Environment**

Certifications	IEC UL Listed
	CSA

## Ordering and shipping details

Category	US10DE200935
Discount Schedule	0DE2
Gtin	3606486287453
Returnability	Yes
Country Of Origin	IIS

## **Packing Units**

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.44 in (21.433 cm)
Package 1 Width	11.13 in (28.258 cm)
Package 1 Length	17.13 in (43.498 cm)
Package 1 Weight	15.12 lb(US) (6.86 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

	Mercury Free
	Rohs Exemption Information Yes
	Pvc Free
<b>⊘</b>	Halogen Free Plastic Parts Product

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov