

# Product data sheet

Specifications



Unit substation, Mini Power-Zone, bolt on, 15kVA, 3 phase, 480V primary, 208Y/120V secondary, 18kA, CC

MPZB15T2F

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 12,610.00 USD

## Main

Product	Sealed Transformer
Certifications	UL Listed
Type	Mini Power-Zone
Enclosure Code	CC
Insulation Temperature	365 °F (185 °C)
Phase	3 phase
Primary Voltage	480 V
Secondary Voltage	208Y/120 V
Full Capacity Taps	2 5 % FCBN
Power Rating	15 kVA
Temperature Rise	115 °C
Winding Material	Copper
Interrupt Rating	18 kA
Circuit Breaker Type	FAL34040 primary main breaker 40 A QO360 secondary main breaker 60 A QO/QOB feeder breaker 40 A
Interior Type	NQ Panelboard interior
Number Of Spaces Available	27
Number Of Circuits	27
Enclosure Type	NEMA 3R hot-rolled steel

## Ordering and shipping details

Category	US10PE216276
Discount Schedule	0PE2
Gtin	785901084334
Returnability	No
Country Of Origin	US

## Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	21.18 in (53.8 cm)
Package 1 Width	54.02 in (137.2 cm)
Package 1 Length	32.20 in (81.8 cm)
Package 1 Weight	510.00 lb(US) (231.332 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

✓ Mercury Free	
✓ Rohs Exemption Information	Yes
✓ Pvc Free	
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel (Metallic), which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>