





Panelboard interior, NQ, main lugs, 400A, Al bus, 54 pole spaces, 3 phase, 4 wire, 240VAC, 48VDC

NQ454L4

Product availability: Stock - Normally stocked in distribution facility

Price*: 2,162.00 USD

Main

Panelboard Type	Main lugs
Product Or Component Type	Interiors
Branch Circuit Breaker Type	QOB QOB-VH QHB
Busbar Material	Aluminium

Complementary

Complementary	
Number Of Spaces	54
Line Rated Current	400 A
[lu] Rated Interrupted Current	10 kA
	22 kA
	65 kA
Wiring Configuration	4-wire
Number Of Phases	3 phase
Voltage Rating	240 V AC
	48 V DC
Connections - Terminals	Lug line AWG 1/0750 kcmil aluminium
	Lug neutral AWG 1/0750 kcmil aluminium
Tightening Torque	274.99300.04 lbf.in (31.0733.90 N.m) 0.080.59 in² (53.48380 mm²) (AWG
	1/0750 kcmil)
	274.99300.04 lbf.in (31.0733.90 N.m) 0.080.27 in² (53.48177.3 mm²) (AWG
	1/0350 kcmil)
	549.98 lbf.in (62.14 N.m) 0.080.59 in2 (53.48380 mm2) (AWG 1/0750 kcmil)
	549.98 lbf.in (62.14 N.m) 0.080.24 in ² (53.48152 mm ²) (AWG 1/0300 kcmil)
	375.01 lbf.in (42.37 N.m) 0.080.59 in ² (53.48380 mm ²) (AWG 1/0750 kcmil)
	375.01 lbf.in (42.37 N.m) 0.080.24 in ² (53.48152 mm ²) (AWG 1/0300 kcmil)

Ordering and shipping details

	11 0
Category	US1PE1A09151
Discount Schedule	PE1A
Gtin	785901578109
Returnability	Yes
Country Of Origin	MX

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.30 in (16.0 cm)
Package 1 Width	14.09 in (35.8 cm)
Package 1 Length	56.30 in (143.0 cm)
Package 1 Weight	26.65 lb(US) (12.09 kg)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
Ø	Mercury Free	
②	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov