Specifications



# One asymmetric mounting rail 32x15 L 2000mm, Order by Multiples of 10 units

NSYADR200

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Price\*: 14.92 USD

#### Main

Anwendung	Multi-purpose
Range	Spacial
Product Or Component Type	Rail
Accessory / Separate Part Category	Mounting accessory
Type Of Rail	Asymmetrical DIN rail
Enclosure Nominal Dimensions	-
Range Compatibility	Spacial Thalassa
Device Composition	1 rail
Quantity Per Set	Set of 10

#### Complementary

Material	galvanised steel
Surface Finish	Not perforated
Fixing Mode	By fixing element - structure of enclosure
Adjustment	Continuous adjustment Pitch 25 mm
Length	78.74 in (2000 mm)
Height	Nominal 0.59 in (15 mm)
Width	Nominal 1.26 in (32 mm)
Thickness	0.06 in (1.5 mm)

## Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480180194
Returnability	No
Country Of Origin	ES

#### **Packing Units**

Unit Type Of Package 1

PCE

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	5.91 in (15.0 cm)
Package 1 Width	12.60 in (32.0 cm)
Package 1 Length	787.40 in (2000.0 cm)
Package 1 Weight	3.20 lb(US) (1.45 kg)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	20
Package 2 Height	2.99 in (7.6 cm)
Package 2 Width	3.54 in (9.0 cm)
Package 2 Length	79.13 in (201.0 cm)
Package 2 Weight	63.93 lb(US) (29.0 kg)
Unit Type Of Package 3	PAL
Number Of Units In Package 3	600
Package 3 Height	19.69 in (50.0 cm)
Package 3 Width	78.74 in (200.0 cm)
Package 3 Length	47.24 in (120.0 cm)
Package 3 Weight	1918.02 lb(US) (870.0 kg)

### **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

# Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations