


Product data sheet

Specifications



Frame : 635x185mm for
sidebyside mounting of WM encl.
from H600 and D300mm.IP 66

NSYAEUBU61SC

Product availability: Non-Stock - Not normally stocked in
distribution facility

Price*: 51.68 USD

Main

Range	Spacial
Accessory / Separate Part Category	Coupling accessory
Product Or Component Type	Coupling frame
Anwendung	Multi-purpose
Mounting Location	Side coupling of 2 enclosures
Range Compatibility	Spacial Spacial S3D compact enclosure Spacial Spacial CRN compact enclosure
Device Composition	1 coupling frame fixing elements
Quantity Per Set	Set of 1

Complementary

Material	Coupling frame polyester charged with fibreglass
Net Weight	2.87 lb(US) (1.3 kg)
Fixing Mode	By screw
Height	25.00 in (635 mm)
Width	7.28 in (185 mm)
Depth	0.77 in (19.5 mm)
Ip Degree Of Protection	IP66
Mounting Diameter	0.00 in (0 mm) 0.24 in (6 mm)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480198953
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	1.38 in (3.5 cm)
Package 1 Width	7.87 in (20.0 cm)
Package 1 Length	25.59 in (65.0 cm)
Package 1 Weight	2.87 lb(US) (1.3 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations