Product data sheet

Specifications





Spacial SF rear panel external fixing - 1800x1200 mm

NSYBP1812

Product availability: Stock - Normally stocked in distribution facility

Price*: 315.44 USD

Main

| Range | Spacial |
|---------------------------------------|---------------------|
| Accessory / Separate Part Category | Enclosure accessory |
| Product Or Component Type | Rear panel |
| Application | Multi-purpose |
| For Enclosure Nominal Dimensions | - |
| Mounting Location | Rear of enclosure |
| Quantity Per Set | Set of 1 |

Complementary

| Range Compatibility | Spacial Spacial SF |
|---------------------|---------------------------------------------------|
| Device Composition | fixing elements 1 rear panel |
| Material | steel |
| Color | Gray RAL 7035) |
| Surface Finish | Epoxy-polyester powder |
| Fixing Mode | By screws captive - from the outside of enclosure |
| Height | Nominal: 70.87 in (1800 mm) |
| Width | Nominal: 47.24 in (1200 mm) |

Ordering and shipping details

| | - |
|-------------------|---------------|
| Category | US10ES180035 |
| Discount Schedule | 0ES1 |
| Gtin | 3606485119236 |
| Returnability | No |
| Country Of Origin | ES |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|---------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 1.38 in (3.5 cm) |
| Package 1 Width | 46.26 in (117.5 cm) |
| Package 1 Length | 70.87 in (180.0 cm) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Package 1 Weight | 63.93 lb(US) (29.0 kg) |
|------------------------------|---------------------------|
| Unit Type Of Package 2 | P2M |
| Number Of Units In Package 2 | 15 |
| Package 2 Height | 24.41 in (62.0 cm) |
| Package 2 Width | 78.74 in (200.0 cm) |
| Package 2 Length | 47.24 in (120.0 cm) |
| Package 2 Weight | 1003.10 lb(US) (455.0 kg) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|------------------------------------------------------------------------------------------------------|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |