

# Product data sheet

Specifications



## Horizontal keyboard shelf 500x195.7 mm. For SPACIAL S3CM HMI encl.RAL7035

NSYCMBPT

⚠ Discontinued on: Apr 19, 2023

⚠ Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

### Main

|                                    |                                                                                                  |
|------------------------------------|--------------------------------------------------------------------------------------------------|
| Range                              | Thalassa                                                                                         |
| Accessory / Separate Part Category | Installation accessory                                                                           |
| Product Or Component Type          | Support                                                                                          |
| Application                        | Multi-purpose                                                                                    |
| For Enclosure Nominal Dimensions   | -                                                                                                |
| Mounting Support                   | Horizontal support, installation on the left or right rail of the frame of the control enclosure |
| Range Compatibility                | Spacial Spacial S3CM                                                                             |
| Device Composition                 | fixing elements<br>1 support                                                                     |
| Quantity Per Set                   | Set of 1                                                                                         |

### Complementary

|                |                        |
|----------------|------------------------|
| Material       | steel                  |
| Color          | Gray RAL 7035)         |
| Surface Finish | Epoxy-polyester powder |
| Height         | 0.85 in (21.5 mm)      |
| Width          | 19.69 in (500 mm)      |
| Depth          | 7.70 in (195.7 mm)     |
| Thickness      | 0.06 in (1.5 mm)       |
| Net Weight     | 5.09 lb(US) (2.307 kg) |

### Ordering and shipping details

|                   |               |
|-------------------|---------------|
| Category          | US10ES180036  |
| Discount Schedule | 0ES1          |
| Gtin              | 3606480213236 |
| Returnability     | No            |
| Country Of Origin | ES            |

### Packing Units

|                        |     |
|------------------------|-----|
| Unit Type Of Package 1 | PCE |
|------------------------|-----|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

---

|                                     |                        |
|-------------------------------------|------------------------|
| <b>Number Of Units In Package 1</b> | 1                      |
| <b>Package 1 Height</b>             | 1.57 in (4.0 cm)       |
| <b>Package 1 Width</b>              | 19.69 in (50.0 cm)     |
| <b>Package 1 Length</b>             | 7.87 in (20.0 cm)      |
| <b>Package 1 Weight</b>             | 5.09 lb(US) (2.307 kg) |

---

## **Contractual warranty**

---

|                 |           |
|-----------------|-----------|
| <b>Warranty</b> | 18 months |
|-----------------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

## Certifications & Standards

**Reach Regulation**

[REACH Declaration](#)

**Eu Rohs Directive**

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

**China Rohs Regulation**

[China RoHS declaration](#)

Pro-active China RoHS declaration (out of China RoHS legal scope)

**Environmental Disclosure**

[Product Environmental Profile](#)

**Circularity Profile**

No need of specific recycling operations