

Symmetric C-shaped rails 40x20x24. Length 2000mm. Supply: 20 rails 2m.

NSYCN40

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 21.62 USD

### Main

Anwendung	Multi-purpose	
Range	Spacial	
Product Or Component Type	Rail	
Accessory / Separate Part Category	Part Mounting accessory	
Type Of Rail	Symmetrical C-shaped	
<b>Enclosure Nominal Dimensions</b>	-	
Range Compatibility	Spacial Thalassa	
Device Composition	1 rail	
Quantity Per Set	Set of 10	

## Complementary

	<u> </u>
Material	galvanised steel
Surface Finish	Not perforated
Fixing Mode	By fixing element
Length	78.74 in (2000 mm)
Height	1.57 in (40 mm)
Width	0.79 in (20 mm)
Thickness	0.06 in (1.5 mm)

# Ordering and shipping details

Category	US10ES180036	
Discount Schedule	0ES1	
Gtin	3606480181092	
Returnability	No	
Country Of Origin	ES	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.79 in (2.0 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Width	1.57 in (4.0 cm)
Package 1 Length	78.74 in (200.0 cm)
Package 1 Weight	4.46 lb(US) (2.025 kg)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	20
Package 2 Height	4.53 in (11.5 cm)
Package 2 Width	3.94 in (10.0 cm)
Package 2 Length	79.13 in (201.0 cm)
Package 2 Weight	89.29 lb(US) (40.5 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations