Specifications



Panelboard interior, NF, main lugs only, 400A, Cu bus, 42 pole spaces, 3 phase, 4 wire, 480Y/277 VAC bolt on

NFOM442L4CHD2

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 3,360.00 USD

Main

Panelboard Type	Main lugs
Branch Circuit Breaker Type	EDB/EDG/EDJ
Busbar Material	Copper

Complementary

42	
400 A	
65 kA	
4-wire 3 phase 480Y/277 V AC	
	Lug line AWG 1/0750 kcmil aluminium Lug neutral AWG 1/0750 kcmil aluminium
	274.99300.04 lbf.in (31.0733.90 N.m) 0.080.59 in ² (53.48380 mm ²) (AWG 1/0750 kcmil) 274.99300.04 lbf.in (31.0733.90 N.m) 0.080.27 in ² (53.48177.3 mm ²) (AWG 1/0350 kcmil) 549.98 lbf.in (62.14 N.m) 0.080.59 in ² (53.48380 mm ²) (AWG 1/0750 kcmil)
549.98 lbf.in (62.14 N.m) 0.080.24 in² (53.48152 mm²) (AWG 1/0300 kcmil) 375.01 lbf.in (42.37 N.m) 0.080.59 in² (53.48380 mm²) (AWG 1/0750 kcmil) 375.01 lbf.in (42.37 N.m) 0.080.24 in² (53.48152 mm²) (AWG 1/0300 kcmil)	
31 in (787.40 mm)	
10.44 in (265.18 mm)	

Environment

Standards

CSA UL

Ordering and shipping details

Category	US1PE1A08337	
Discount Schedule	PE1A	
Gtin	785901672333	
Returnability	No	
Country Of Origin	MX	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	34.00 lb(US) (15.422 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

REACh Declaration
Compliant
EU RoHS Declaration
China RoHS declaration
Pro-active China RoHS declaration (out of China RoHS legal scope)
Product Environmental Profile
No need of specific recycling operations
WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov