Product data sheet

Specifications





Climasys Ultra thin resistance heater low starting current 195W 120V 400x650mm

NSYCRS200W120V

(!) Discontinued on: Mar 11, 2022



Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	ClimaSys
Product Name	ClimaSys CR
Product Or Component Type	Ultra thin resistance heater
Power Range	195 W
Input Voltage	120 V AC 50/60 Hz
Flectrical Connection	Cable 6 56 ft (2 m)

Complementary

Operating Position	Horizontal	
	Vertical	
Ambient Air Temperature For Operation	-76158 °F (-6070 °C)	
Temperature Setting Range	-40158 °F (-4070 °C)	
Material	silicone rubber	
Height	External 14.96 in (380 mm)	
Width	External 25.59 in (650 mm)	
Depth	External 0.06 in (1.6 mm)	
Device Composition	6 self-adhesive Velcro pads	
	6 plastic spacers	
	4 Telequick nuts	
	4 clip-on nuts	
	fixing accessories	
Condition Of Use	Air sealed enclosure	
	Electrical protection is needed	
	Heaters must be installed with a thermal controller	
Fixing Mode	By 4 screws	
Mounting Support	Telequick mounting plate	
	Adhesive Velcro	
	DIN rail	
	Standard mounting plate	

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480530197
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Apr 25, 2024 Life Is On Schneider 1

Country Of Origin DE

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Product out of China RoHS scope. Substance declaration for your information.
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.