# Product data sheet






## Climasys Ultra thin resistance heater low starting current 20W 120V 130x250mm

NSYCRS25W120V

Discontinued on: Mar 15, 2022



Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Range	ClimaSys
Product Name	ClimaSys CR
Product Or Component Type	Ultra thin resistance heater
Power Range	25 W
Input Voltage	120 V AC 50/60 Hz
Electrical Connection	Cable 6.56 ft (2 m)

### Complementary

Operating Position	Vertical Horizontal
Ambient Air Temperature For Operation	-76158 °F (-6070 °C)
Temperature Setting Range	-40158 °F (-4070 °C)
Material	silicone rubber
Height	External 4.33 in (110 mm)
Width	External 9.06 in (230 mm)
Depth	External 0.06 in (1.6 mm)
Device Composition	6 self-adhesive Velcro pads
	6 plastic spacers
	4 Telequick nuts
	4 clip-on nuts
	fixing accessories
Condition Of Use	Heaters must be installed with a thermal controller
	Air sealed enclosure
	Electrical protection is needed
Fixing Mode	By 4 screws
Mounting Support	Standard mounting plate
	DIN rail
	Adhesive Velcro
	Telequick mounting plate

## Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480530135
Returnability	Yes

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Country Of Origin DE

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

## Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Product out of China RoHS scope. Substance declaration for your information.
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.