



One asymmetric mounting rail perforated 32x15 L2000mm, Order by Multiples of 10 units

NSYADR200D

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 17.95 USD

Main

Anwendung	Multi-purpose
Range	Spacial
Product Or Component Type	Rail
Accessory / Separate Part Category	Mounting accessory
Type Of Rail	Asymmetrical DIN rail
Enclosure Nominal Dimensions	-
Range Compatibility	Spacial Thalassa
Device Composition	1 rail
Quantity Per Set	Set of 10

Complementary

Material	galvanised steel
Surface Finish	Perforated
Fixing Mode	By fixing element - structure of enclosure
Adjustment	Continuous adjustment Pitch 25 mm
Length	78.74 in (2000 mm)
Height	Nominal 0.59 in (15 mm)
Width	Nominal 1.26 in (32 mm)
Thickness	0.06 in (1.5 mm)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480180200
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1 PCE

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	0.59 in (1.5 cm)
Package 1 Width	1.26 in (3.2 cm)
Package 1 Length	78.74 in (200.0 cm)
Package 1 Weight	2.87 lb(US) (1.3 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations