

Product data sheet

Specifications



Earth leads section 6mm², length 160mm, eyelet hole 6,4mm.
Packaging unit: 10.

NSYEL166D6

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 12.75 USD

Main

Range	Spacial
Anwendung	Multi-purpose
Product Or Component Type	Earthing wire
Device Composition	1 lead
Quantity Per Set	Set of 10

Complementary

Material	PVC (polyvinyl chloride) green and yellow sheath Brass and copper alloy terminal
Fixing Mode	Nut and washer - on earth connection
Length	6.30 in (160 mm)
Width	0.39 in (10 mm)
Nominal Cross Section	0.01 in² (6 mm²)
Diameter	0.25 in (6.4 mm)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480181627
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.39 in (1 cm)
Package 1 Width	4.13 in (10.5 cm)
Package 1 Length	7.87 in (20 cm)
Package 1 Weight	0.46 oz (13 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Height	7.87 in (20 cm)
Package 2 Width	4.13 in (10.5 cm)
Package 2 Length	0.39 in (1 cm)
Package 2 Weight	4.73 oz (134 g)
Unit Type Of Package 3	P12
Number Of Units In Package 3	9600
Package 3 Height	22.05 in (56 cm)
Package 3 Width	31.50 in (80 cm)
Package 3 Length	47.24 in (120 cm)
Package 3 Weight	335.32 lb(US) (152.1 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations