# Product data sheet

Specification





### Inner door, PanelSeT SFN, Spacial SF, Spacial SM, for electrical enclosure H1600 W600mm

NSYID166

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 565.49 USD

#### Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Door
Application	Multi-purpose
For Enclosure Nominal Dimensions	-
Mounting Location	Front
Range Compatibility	Spacial Spacial SF Spacial Spacial SM
Device Composition	1 door 2 lock with 3 mm double bar insert 1 handle fixing elements
Quantity Per Set	Set of 1

### Complementary

Material	sheet steel
Color	Gray RAL 7035)
Surface Finish	Epoxy-polyester powder
Lock Type	Lock 3 mm double bar
Number Of Locks	2
Adjustment	Adjustable in depth every 25 mm
Door Type	Internal plain
Door Opening Side	Reversible
Maximum Load	15 kg/m²
Height	Nominal 62.99 in (1600 mm) Real 57.68 in (1465 mm)
Width	Nominal 23.62 in (600 mm) Real 19.69 in (500 mm)
Depth	0.77 in (19.5 mm)

#### Ordering and shipping details

Category US10ES180036

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Discount Schedule	0ES1
Gtin	3606485126999
Returnability	No
Country Of Origin	ES

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.76 in (7.0 cm)
Package 1 Width	22.05 in (56.0 cm)
Package 1 Length	60.24 in (153.0 cm)
Package 1 Weight	28.66 lb(US) (13.0 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations