

Product data sheet

Specifications



Lower cable guide crossrail,
PanelSeT SFN, PanelSet SF,
PanelSet SM, for electrical
enclosure W600mm

NSYCFP60

Product availability: Non-Stock - Not normally stocked in
distribution facility

Price*: 89.03 USD

Main

| | |
|-----------------------------------|-------------------|
| Range | PanelSeT |
| Category | Cabling accessory |
| Product Or Component Type | Cable guide |
| Application | Multi-purpose |
| Nominal Dimensions Of The Housing | - |

Complementary

| | |
|---------------------|--|
| Mounting Location | On structure of enclosure |
| Range Compatibility | PanelSeT PanelSeT SF PanelSeT PanelSeT SM PanelSeT PanelSeT SFX PanelSeT PanelSeT SMX |
| Device Composition | fixing elements 1 rail |
| Quantity Per Set | Set of 1 |
| Material | galvanised steel |
| Adjustment | Adjustable in depth every 25 mm |
| Fixing Center | 550 mm |
| Width | Nominal: 23.62 in (600 mm) |

Ordering and shipping details

| | |
|-------------------|---------------|
| Category | US10ES180036 |
| Discount Schedule | 0ES1 |
| Gtin | 3606480063268 |
| Returnability | No |
| Country Of Origin | FR |

Packing Units

| | |
|------------------------------|------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 2.95 in (7.5 cm) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|--------------------------|
| Package 1 Width | 3.15 in (8.0 cm) |
| Package 1 Length | 29.13 in (74.0 cm) |
| Package 1 Weight | 3.36 lb(US) (1.522 kg) |
| Unit Type Of Package 2 | PAM |
| Number Of Units In Package 2 | 80 |
| Package 2 Height | 19.69 in (50.0 cm) |
| Package 2 Width | 39.37 in (100.0 cm) |
| Package 2 Length | 47.24 in (120.0 cm) |
| Package 2 Weight | 304.24 lb(US) (138.0 kg) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

| | |
|--|---|
|  Reach Free Of Svhc | |
|  Toxic Heavy Metal Free | |
|  Mercury Free | |
|  Rohs Exemption Information | Yes |
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |