Product data sheet

Specification





Insulating mounting plate for enclosure H300xW250mm made of bakelite

NSYMB3025

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 10.01 USD

Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Mounting plate
Device Application	Multi-purpose
Enclosure Nominal Dimensions	- H: 11.81 in (300 mm) W: 9.84 in (250 mm)
Mounting Location	Direct fixing on backstuds Step slide
Mounting Plate Description	Plain
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X
Quantity Per Set	Set of 1
Material	bakelite
Color	Black RAL 9005)

Complementary

Fixing Mode	Screwed on backstuds M8 By fixing element
Permanent Permissible Load	4133.67 lb(US) (1875 kg)
Height	10.43 in (265 mm)
Width	7.87 in (200 mm)
Thickness	0.16 in (4 mm)
Net Weight	4.41 lb(US) (2 kg)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480182686
Returnability	No
Country Of Origin	ES

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.16 in (0.4 cm)
Package 1 Width	7.87 in (20.0 cm)
Package 1 Length	10.43 in (26.5 cm)
Package 1 Weight	10.72 oz (304.0 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations