Product data sheet

Specifications





Plain mounting plate H1000xW800mm Galvanised sheet steel Reversible dimension

NSYMM108

Product availability: Stock - Normally stocked in distribution facility

Price*: 124.10 USD

Main

Range	Spacial	
Accessory / Separate Part Category	Mounting accessory	
Product Or Component Type	Mounting plate	
Device Application	Multi-purpose	
Enclosure Nominal Dimensions	- H: 31.50 in (800 mm) W: 39.37 in (1000 mm) - H: 39.37 in (1000 mm) W: 31.50 in (800 mm)	
Mounting Location	Direct fixing on backstuds Step slide	
Mounting Plate Description	Plain	
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X	
Quantity Per Set	Set Set of 1	
Material	galvanised steel	

Complementary

Fixing Mode	Screwed on backstuds M8 By fixing element
Permanent Permissible Load	330.69 lb(US) (150 kg)
Height	37.40 in (950 mm)
Width	29.53 in (750 mm)
Thickness	0.10 in (2.5 mm)
Net Weight	30.78 lb(US) (13.96 kg)
Variant Particularity	Installation in enclosures with inverted dimensions

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480183164
Returnability	Yes
Country Of Origin	US

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.12 in (0.3 cm)
Package 1 Width	29.72 in (75.5 cm)
Package 1 Length	37.40 in (95.0 cm)
Package 1 Weight	30.58 lb(US) (13.87 kg)
Unit Type Of Package 2	P12
Number Of Units In Package 2	40
Package 2 Height	47.24 in (120 cm)
Package 2 Width	31.50 in (80 cm)
Package 2 Length	15.35 in (39 cm)
Package 2 Weight	1254.43 lb(US) (569 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations