Product data sheet





Fixing sloping on enclosure, square 50 mm. For SPACIAL S3CM HMI encl.

NSYCMUCP50

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1,639.77 USD

Main

| Range | Spacial | |
|---------------------------------------|--|--|
| Accessory / Separate Part Category | Cable management accessory | |
| Product Or Component Type | Bent and rotating enclosure fixing | |
| Device Application | Multi-purpose | |
| Enclosure Nominal Dimensions | s - | |
| Mounting Location | Location On enclosure | |
| Mounting Support | For 50 mm square tube On enclosures with a depth of 300 mm requires an adaptor On enclosures with depths of 200 and 250 mm | |
| Range Compatibility | Spacial Spacial S3CM | |
| Device Composition | fixing elements 1 tilting fixing | |
| Quantity Per Set | Set of 1 | |

Complementary

| Material | aluminium | |
|----------------------------|------------------------|--|
| Color | Gray RAL 7040) | |
| Surface Finish | Epoxy-polyester powder | |
| Fixing Mode | By fixing element | |
| Operating Angle | 30 ° | |
| Permanent Permissible Load | 6.57 lb(US) (2.98 kg) | |
| Height | 7.17 in (182 mm) | |
| Width | 3.94 in (100 mm) | |
| Depth | 3.94 in (100 mm) | |
| Net Weight | 6.53 lb(US) (2.96 kg) | |

Ordering and shipping details

| Category | US10ES180036 |
|-------------------|---------------|
| Discount Schedule | 0ES1 |
| Gtin | 3606480213090 |
| Returnability | No |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Country Of Origin ES

Packing Units

| _ | |
|------------------------------|-------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 5.31 in (13.5 cm) |
| Package 1 Width | 6.50 in (16.5 cm) |
| Package 1 Length | 8.27 in (21.0 cm) |
| Package 1 Weight | 6.98 lb(US) (3.168 kg) |
| Unit Type Of Package 2 | PAL |
| Number Of Units In Package 2 | 10 |
| Package 2 Height | 11.42 in (29.0 cm) |
| Package 2 Width | 14.76 in (37.5 cm) |
| Package 2 Length | 47.24 in (120.0 cm) |
| Package 2 Weight | 69.84 lb(US) (31.68 kg) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| Ø | Reach Free Of Svhc | |
|----------|----------------------------|-----|
| Ø | Toxic Heavy Metal Free | |
| ② | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |