



## Plain mounting plate H250xW500mm made of galvanised sheet steel

NSYMM2550

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 27.66 USD

#### Main

Range	Spacial	
Accessory / Separate Part Category	Mounting accessory	
Product Or Component Type	Mounting plate	
Device Application	Multi-purpose	
<b>Enclosure Nominal Dimensions</b>	-	
Mounting Location	Direct fixing on backstuds Step slide	
Mounting Plate Description	Plain	
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X	
Quantity Per Set	Set of 1	
Material	galvanised steel	

## Complementary

Fixing Mode	Screwed on backstuds M8 By fixing element	
Permanent Permissible Load	132.28 lb(US) (60 kg)	
	7.87 in (200 mm)	
Width	17.72 in (450 mm)	
Thickness	0.07 in (1.8 mm)	
Net Weight	2.87 lb(US) (1.3 kg)	

## Ordering and shipping details

Category	US10ES180036	
Discount Schedule	0ES1	
Gtin	3606480183263	
Returnability	No	
Country Of Origin	ES	

#### **Packing Units**

Unit Type Of Package 1 PCE

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1	
Package 1 Height	0.12 in (0.3 cm)	
Package 1 Width	7.87 in (20 cm)	
Package 1 Length	17.72 in (45 cm)	
Package 1 Weight	2.69 lb(US) (1.222 kg)	
Unit Type Of Package 2	PAM	
Number Of Units In Package 2	200	
Package 2 Height	21.65 in (55 cm)	
Package 2 Width	39.37 in (100 cm)	
Package 2 Length	47.24 in (120 cm)	
Package 2 Weight	566.59 lb(US) (257 kg)	

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>Ø</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations