

Product data sheet

Specifications



Fixed subbase, square 50 mm, for SPACIAL S3CM HMI encl. RAL 7040.

NSYCMUMR50

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 279.07 USD

Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Fixing on support
Device Application	Multi-purpose
Enclosure Nominal Dimensions	-
Mounting Location	Between tube and support
Mounting Support	Option of passing cables through the inside For 50 mm square tube
Range Compatibility	Spacial Spacial S3CM
Device Composition	fixing elements 1 fixed base
Quantity Per Set	Set of 1

Complementary

Material	moulded steel
Color	Gray RAL 7040)
Surface Finish	Epoxy-polyester powder
Fixing Mode	By screw M12 - fixed base
Permanent Permissible Load	7.17 lb(US) (3.25 kg)
Height	4.33 in (110 mm)
Width	5.98 in (152 mm)
Depth	5.98 in (152 mm)
Diameter	5.98 in (152 mm)
Net Weight	7.72 lb(US) (3.5 kg)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480212987
Returnability	No
Country Of Origin	ES

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.31 in (13.5 cm)
Package 1 Width	6.50 in (16.5 cm)
Package 1 Length	6.50 in (16.5 cm)
Package 1 Weight	7.72 lb(US) (3.5 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	50
Package 2 Height	19.69 in (50.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	423.29 lb(US) (192.0 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

China Rohs Regulation

[China RoHS declaration](#)

Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations