## **Product data sheet**

Specification





Fixed subbase, square 80 mm, for SPACIAL S3CM HMI encl. RAL 7040.

NSYCMUMR80

! Discontinued on: Dec 31, 2023

① To be discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 490.47 USD

#### Main

Range	Spacial	
Accessory / Separate Part Category	Mounting accessory	
Product Or Component Type	Fixing on support	
Device Application	Multi-purpose	
Enclosure Nominal Dimensions	-	
Mounting Location	Between tube and support	
Mounting Support	For 80 mm square tube Option of passing cables through the inside	
Range Compatibility	Spacial Spacial S3CM	
Device Composition	fixing elements 1 fixed base	
Quantity Per Set	Set of 1	

#### Complementary

Material	moulded steel	
Color	Gray RAL 7040)	
Surface Finish	Epoxy-polyester powder	
Fixing Mode	By screw M12 - fixed base	
Permanent Permissible Load	15.43 lb(US) (7 kg)	
Height	8.07 in (205 mm)	
Width	8.66 in (220 mm)	
Depth	6.97 in (177 mm)	
Diameter	7.91 in (201 mm)	
Net Weight	15.92 lb(US) (7.22 kg)	

### Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480212970

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	No	
Country Of Origin	FS	

# **Packing Units**

_		
Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	8.07 in (20.5 cm)	
Package 1 Width	8.66 in (22.0 cm)	
Package 1 Length	9.45 in (24.0 cm)	
Package 1 Weight	16.98 lb(US) (7.7 kg)	
Unit Type Of Package 2	PAM	
Number Of Units In Package 2	20	
Package 2 Height	14.57 in (37.0 cm)	
Package 2 Width	39.37 in (100.0 cm)	
Package 2 Length	47.24 in (120.0 cm)	
Package 2 Weight	368.17 lb(US) (167.0 kg)	

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>Ø</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	No need of specific recycling operations	