# **Product data sheet**

Specifications





# Mounting pillar for Spacial S3D encl. RAL7035. H800m.

NSYCOCN80

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 258.41 USD

#### Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Support pillar device
Device Application	Multi-purpose
Enclosure Nominal Dimensions	-
Mounting Location	Bottom face of the enclosure
Mounting Support	With adaptation plate
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN
Device Composition	fixing elements 1 support pillar
Quantity Per Set	Set of 1

### Complementary

Material	extruded aluminium
Color	Gray RAL 7035)
Surface Finish	Epoxy-polyester powder
Fixing Mode	By fixing element - on adaptation plate
Permanent Permissible Load	0.00 lb(US) (0 kg)
Height	Nominal 31.50 in (800 mm) Foot height 29.25 in (743 mm) Base height 2.17 in (55 mm)
Width	Base width 14.57 in (370 mm) Fixing centers to floor 12.99 in (330 mm) Foot width 4.02 in (102 mm)
Depth	Base depth 9.84 in (250 mm) Fixing centers to floor 6.30 in (160 mm) Foot depth 2.56 in (65 mm)
Net Weight	8.38 lb(US) (3.8 kg)

## Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480211669
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin ES

# **Packing Units**

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.91 in (15.000 cm)
Package 1 Width	10.63 in (27.000 cm)
Package 1 Length	29.72 in (75.500 cm)
Package 1 Weight	8.95 lb(US) (4.059 kg)
Unit Type Of Package 2	P12
Number Of Units In Package 2	8
Package 2 Height	17.72 in (45.000 cm)
Package 2 Width	31.50 in (80.000 cm)
Package 2 Length	47.24 in (120.000 cm)
Package 2 Weight	98.04 lb(US) (44.472 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations