Product data sheet





Silkscreened plain mounting plate H500xW400mm made of galvanised sheet steel

NSYMS54

! Discontinued on: Jun 28, 2023



Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	Spacial	
Accessory / Separate Part Category	Mounting accessory	
Product Or Component Type	Mounting plate	
Device Application	Multi-purpose	
Enclosure Nominal Dimensions	minal Dimensions - H: 19.69 in (500 mm) W: 15.75 in (400 mm)	
Mounting Location	Step slide Direct fixing on backstuds	
Mounting Plate Description	te Description Plain	
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X	
Quantity Per Set	er Set Set of 1	
Material	galvanised steel	
Surface Finish	Silkscreened	

Complementary

Fixing Mode	Screwed on backstuds M8 By fixing element	
Permanent Permissible Load	198.42 lb(US) (90 kg)	
Height	17.72 in (450 mm)	
Width	13.78 in (350 mm)	
Depth	4.92 in (125 mm)	
Thickness	0.08 in (2 mm)	
Net Weight	5.50 lb(US) (2.494 kg)	
Variant Particularity	Centimetric grid pattern	

Ordering and shipping details

Category	US10ES180036	
Discount Schedule	0ES1	
Gtin	3606480183829	
Returnability	No	
Country Of Origin	FR	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	0.08 in (0.2 cm)	
Package 1 Width	13.78 in (35 cm)	
Package 1 Length	17.72 in (45 cm)	
Package 1 Weight	5.15 lb(US) (2.334 kg)	
Unit Type Of Package 2	P12	
Number Of Units In Package 2	140	
Package 2 Height	tht 14.57 in (37 cm)	
Package 2 Width	31.50 in (80 cm)	
Package 2 Length	47.24 in (120 cm)	
Package 2 Weight	749.57 lb(US) (340 kg)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations