# Product data sheet

Specifications





# set of 4 Spacial SF/SM brackets to install equipment 1U or 3U high

NSYRC1U

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 96.15 USD

#### Main

Range	Spacial	
Accessory / Separate Part Category	Enclosure accessory	
Product Or Component Type	Support	
Application	Electronic application Multi-purpose	
For Enclosure Nominal Dimensions	-	
Mounting Support	Direct to the structure, Spacial SF Enclosure, Spacial SM with vertical adaptor section	
Range Compatibility	Spacial Spacial SF Spacial Spacial SM Spacial Spacial SF-E	
Device Composition	fixing elements 2 right support 2 left support	
Quantity Per Set Set of 1		

## Complementary

Material	steel
Surface Finish	Zinc coated
Fixing Mode	By clips structure of enclosure By screws
Adjustment	Adjustable in height with a pitch of 25 mm
Number Of Units 19"	1
Height	1.75 in (44.45 mm)
Depth	2.87 in (73 mm)

### Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480066764
Returnability	No
Country Of Origin	ES

### **Packing Units**

CE

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	2.17 in (5.5 cm)
Package 1 Width	3.35 in (8.5 cm)
Package 1 Length	5.31 in (13.5 cm)
Package 1 Weight	8.11 oz (230.0 g)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations