# Product data sheet





## set of 4 Spacial SF support brackets for 19" fixed rack - 400kg load - 600 mm

NSYRCKS6

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 96.71 USD

#### Main

Range	Spacial	
Accessory / Separate Part Category	Enclosure accessory	
Product Or Component Type	Support bracket	
Application	Electronic application	
For Enclosure Nominal Dimensions	-	
Mounting Support	19" fixed rack	
Range Compatibility	Spacial Spacial SF-E	
<b>Device Composition</b>	nposition fixing elements 4 support	
Quantity Per Set	Set of 1	

### Complementary

Material	el	
Surface Finish	Zinc coated	
Fixing Mode	By fixing element	
Permanent Permissible Load	881.85 lb(US) (400 kg)	
Height	1.97 in (50 mm)	
Depth	Nominal 23.62 in (600 mm)	

### Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480066962
Returnability	No
Country Of Origin	ES

### **Packing Units**

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	1.97 in (5.0 cm)	
Package 1 Width	1.97 in (5.0 cm)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Length	23.62 in (60.0 cm)
Package 1 Weight	5.95 lb(US) (2.7 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations