## Product data sheet

Specifications





# One symmetric mounting rail perforated 35x15 L2000mm, Order by Multiples of 10 units

NSYSDR200D

Product availability: Stock - Normally stocked in distribution

Price\*: 11.74 USD

#### Main

Anwendung	Multi-purpose
Range	Spacial
Product Or Component Type	Rail
Accessory / Separate Part Category	Mounting accessory
Type Of Rail	Symmetrical DIN
<b>Enclosure Nominal Dimensions</b>	-
Range Compatibility	Spacial Thalassa
Device Composition	1 rail
Quantity Per Set	Set of 10

### Complementary

Material	galvanised steel
Surface Finish	Perforated
Fixing Mode	By fixing element - structure of enclosure
Adjustment	Pitch 25 mm Continuous adjustment
Length	78.74 in (2000 mm)
Height	Nominal 0.59 in (15 mm)
Width	Nominal 1.38 in (35 mm)
Thickness	0.06 in (1.5 mm)

## Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480184345
Returnability	Yes
Country Of Origin	ES

## **Packing Units**

Unit Type Of Package 1 PCE

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	0.67 in (1.700 cm)
Package 1 Width	1.30 in (3.300 cm)
Package 1 Length	78.74 in (200.000 cm)
Package 1 Weight	2.65 lb(US) (1.200 kg)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	1.57 in (4.000 cm)
Package 2 Width	3.35 in (8.500 cm)
Package 2 Length	78.94 in (200.500 cm)
Package 2 Weight	26.90 lb(US) (12.200 kg)
Unit Type Of Package 3	P2M
Number Of Units In Package 3	300
Package 3 Height	17.72 in (45.000 cm)
Package 3 Width	78.74 in (200.000 cm)
Package 3 Length	47.24 in (120.000 cm)
Package 3 Weight	826.73 lb(US) (375.000 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>9</b>	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

## **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations