# Product data sheet

Specifications





# Spacial SF transparent door - 2000x1000 mm

NSYSFD2010T

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 766.78 USD

#### Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Door
Application	Multi-purpose
For Enclosure Nominal Dimensions	-
Mounting Location	Front
Range Compatibility	Spacial Spacial SF
Device Composition	door     lock with handle and 5 mm double bar insert     locking bar system 4 points     hinges     locking bar catches
Quantity Per Set	Set of 1

### Complementary

Material	Door Securit glass Door sheet steel
Color	Gray RAL 7035)
Surface Finish	Epoxy-polyester powder
Lock Type	Lock 5 mm double bar
Number Of Locks	1
Door Type	External transparent
Door Opening Side	Reversible 120 °)
Height	Nominal: 78.74 in (2000 mm)
Width	Nominal: 39.37 in (1000 mm)

# Ordering and shipping details

Category	US10ES180035
Discount Schedule	0ES1
Gtin	3606485119717
Returnability	No
Country Of Origin	ES

# **Packing Units**

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.17 in (5.5 cm)
Package 1 Width	38.58 in (98.0 cm)
Package 1 Length	81.89 in (208.0 cm)
Package 1 Weight	61.73 lb(US) (28.0 kg)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	10
Package 2 Height	28.35 in (72.0 cm)
Package 2 Width	82.68 in (210.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	687.84 lb(US) (312.0 kg)

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations