Product data sheet

Specification





Inner door, PanelSeT SFN, Spacial SF, Spacial SM, for electrical enclosure H2000 W600mm

NSYID206

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 472.42 USD

Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Door
Application	Multi-purpose
For Enclosure Nominal Dimensions	-
Mounting Location	Front
Range Compatibility	Spacial Spacial SFX Spacial Spacial SF Spacial Spacial SM
Device Composition	1 door 2 lock with 3 mm double bar insert 1 handle fixing elements
Quantity Per Set	Set of 1

Complementary

Material	sheet steel
Color	Gray RAL 7035)
Surface Finish	Epoxy-polyester powder
Lock Type	Lock 3 mm double bar
Number Of Locks	2
Adjustment	Adjustable in depth every 25 mm
Door Type	Internal plain
Door Opening Side	Reversible
Maximum Load	15 kg/m²
Height	Nominal 78.74 in (2000 mm) Real 73.43 in (1865 mm)
Width	Nominal 23.62 in (600 mm) Real 19.69 in (500 mm)
Depth	0.77 in (19.5 mm)

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.



Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606485127040
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.76 in (7.0 cm)
Package 1 Width	22.05 in (56.0 cm)
Package 1 Length	75.98 in (193.0 cm)
Package 1 Weight	52.91 lb(US) (24.0 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations