Product data sheet

Specifications





Spacial SF mounting plate fixing brackets

NSYSFPB

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 26.33 USD

Main

Category	Mounting accessory
Product Or Component Type	Fixing bracket
Range Compatibility	Spacial Spacial SF
Application	Multi-purpose
Nominal Dimensions Of The Housing	-
Mounting Location	On structure of enclosure
Product Destination	For mounting plate
Device Composition	4 mounting plate fixing brackets fixing elements
Quantity Per Set	Set of 1
Material	steel

Complementary

Surface Finish	Zinc coated
Fixing Mode	By fixing element
Adjustment	Adjustable in depth every 25 mm
Permanent Permissible Load	1322.77 lb(US) (600 kg)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480078163
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.54 in (9.0 cm)
Package 1 Width	4.33 in (11.0 cm)
Package 1 Length	5.20 in (13.2 cm)
Package 1 Weight	13.05 oz (370.0 g)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Unit Type Of Package 2	РАМ
Number Of Units In Package 2	300
Package 2 Height	37.80 in (96.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	628.32 lb(US) (285.0 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations