

Spacial SF supports for Lutze chassis - 2.5 mm

NSYLSUP

Discontinued on: Jun 30, 2023

(!) Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Support
Application	Multi-purpose
Nominal Dimensions Of The	-

Complementary

Range Compatibility	Spacial Spacial SF	
Mounting Location	Back of enclosure	
Mounting Support	Lutze chassis	
Device Composition	fixing elements 6 supports	
Quantity Per Set	Set of 1	
Material	galvanised steel	
Fixing Mode	By screws - back of enclosure	
Adjustment	Adjustable in height with a pitch of 25 mm	
Height	1.38 in (35 mm)	
Width	1.77 in (45 mm)	
Depth	2.95 in (75 mm)	
Thickness	0.10 in (2.5 mm)	

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480065262
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Height	1.97 in (5.0 cm)	
Package 1 Width	2.36 in (6.0 cm)	
Package 1 Length	3.94 in (10.0 cm)	
Package 1 Weight	32.45 oz (920.0 g)	
Unit Type Of Package 2	PAL	
Number Of Units In Package 2	20	
Package 2 Height	7.87 in (20.0 cm)	
Package 2 Width	11.81 in (30.0 cm)	
Package 2 Length	15.75 in (40.0 cm)	
Package 2 Weight 41.89 lb(US) (19.0 kg)		

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
9	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile