

Product data sheet

Specifications



Microperforated mounting plate H1200xW800 w/holes diam 3,6mm on 12,5mm pitch

NSYMF128

Product availability: Stock - Normally stocked in distribution facility

Price*: 250.71 USD

Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Mounting plate
Device Application	Multi-purpose
Enclosure Nominal Dimensions	- H: 47.24 in (1200 mm) W: 31.50 in (800 mm) - H: 31.50 in (800 mm) W: 47.24 in (1200 mm)
Mounting Location	Step slide Direct fixing on backstuds
Mounting Plate Description	Microperforated
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X
Quantity Per Set	Set of 1
Material	galvanised steel

Complementary

Fixing Mode	Screwed on backstuds M8 By fixing element
Permanent Permissible Load	396.83 lb(US) (180 kg)
Height	45.87 in (1165 mm)
Width	30.12 in (765 mm)
Depth	4.92 in (125 mm)
Thickness	0.10 in (2.5 mm)
Net Weight	37.62 lb(US) (17.064 kg)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480183027
Returnability	Yes
Country Of Origin	ES

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.39 in (1 cm)
Package 1 Width	29.53 in (75 cm)
Package 1 Length	45.28 in (115 cm)
Package 1 Weight	35.27 lb(US) (16 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	25
Package 2 Height	23.62 in (60 cm)
Package 2 Width	39.37 in (100 cm)
Package 2 Length	47.24 in (120 cm)
Package 2 Weight	1004.21 lb(US) (455.5 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations