Product data sheet

Specifications





Plain mounting plate H800xW600mm made of galvanised sheet steel

NSYMM86

Product availability: Stock - Normally stocked in distribution

acility

Price*: 74.82 USD

Overview

Lead Time Usually Ships within 4 Weeks

Main

Range	Spacial	
Accessory / Separate Part Category	Mounting accessory	
Product Or Component Type	Mounting plate	
Device Application	Multi-purpose	
Enclosure Nominal Dimensions	- H: 31.50 in (800 mm) W: 23.62 in (600 mm)	
Mounting Location	Step slide Direct fixing on backstuds	
Mounting Plate Description	Plain	
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X	
Quantity Per Set	Set of 1	
Material	galvanised steel	

Complementary

Fixing Mode	Screwed on backstuds M8 By fixing element	
Permanent Permissible Load	297.62 lb(US) (135 kg)	
Height	29.53 in (750 mm)	
Width	21.65 in (550 mm)	
Thickness	0.10 in (2.5 mm)	
Net Weight	17.79 lb(US) (8.07 kg)	
Variant Particularity	With enclosures H800 x W1200	

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480183430
Returnability	Yes

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.39 in (1.0 cm)
Package 1 Width	21.65 in (55.0 cm)
Package 1 Length	29.53 in (75.0 cm)
Package 1 Weight	19.38 lb(US) (8.792 kg)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	60
Package 2 Height	17.72 in (45.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	1191.64 lb(US) (540.52 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations