# **Product data sheet**

Specifications





Plain mounting plate, PanelSeT SFN, Spacial SF, Spacial SM, for electrical enclosure H2000 W1000mm, galvanized steel

NSYMP2010

Product availability: Stock - Normally stocked in distribution facility

Price\*: 227.00 USD

#### Main

Range	Spacial
Accessory / Separate Part Category	Mounting accessory
Product Or Component Type	Mounting plate
Device Application	Multi-purpose
Enclosure Nominal Dimensions	-
Mounting Plate Description	Plain
Range Compatibility	Spacial Spacial SF Spacial Spacial SM Spacial Spacial SFX Spacial Spacial SMX
Device Composition	1 mounting plate 2 sliding shoes
Quantity Per Set	Set of 1
Material	galvanised steel

### Complementary

Fixing Mode	By fixing brackets
Maximum Load	300 kg/m²
Permanent Permissible Load	1102.31 lb(US) (500 kg) intermediate position 1322.77 lb(US) (600 kg) back of the enclosure
Height	Fixing centers 72.83 in (1850 mm)  Nominal 78.74 in (2000 mm)  Real 74.69 in (1897 mm)
Width	Fixing centers 33.46 in (850 mm)  Nominal 39.37 in (1000 mm)  Real 35.28 in (896 mm)
Depth	1.06 in (27 mm)

### Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606485126913
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin US

## **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.18 in (3.0 cm)
Package 1 Width	35.43 in (90.0 cm)
Package 1 Length	75.20 in (191.0 cm)
Package 1 Weight	83.78 lb(US) (38.0 kg)
Unit Type Of Package 2	P2M
Number Of Units In Package 2	20
Package 2 Height	29.92 in (76.0 cm)
Package 2 Width	78.74 in (200.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	1739.45 lb(US) (789.0 kg)

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>9</b>	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations