

Product data sheet

Specifications



Cover plate, Lineryg TR, 2 level,
2.2mm width, 4 points, for screw
terminals NSYTRV24D, grey, Set of
50

NSYTRACE24

Product availability: Stock - Normally stocked in distribution
facility

Price*: 1.20 USD

Main

Range	Lineryg
Product Name	Lineryg TR
Product Or Component Type	Cover plate
Device Short Name	TRA
Accessory / Separate Part Category	Insulation accessory
Product Compatibility	TRV screw terminal terminal block, length = 2.75 in (69.9 mm)
Thickness	0.09 in (2.2 mm)

Complementary

Cable Cross Section	0.00 in² (2.5 mm²) 0.01 in² (4 mm²)
Number Of Connections	2
Number Of Measurement Input	4 2
Quantity Per Set	Set of 50
Net Weight	0.08 oz (2.2 g)
Color	Gray

Ordering and shipping details

Category	US10CP521715
Discount Schedule	0CP5
Gtin	3606480533457
Returnability	Yes
Country Of Origin	DE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.16 in (0.4 cm)
Package 1 Width	2.28 in (5.8 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	2.76 in (7 cm)
Package 1 Weight	0.14 oz (4 g)
Unit Type Of Package 2	BAG
Number Of Units In Package 2	50
Package 2 Height	1.97 in (5 cm)
Package 2 Width	4.92 in (12.5 cm)
Package 2 Length	10.63 in (27 cm)
Package 2 Weight	8.08 oz (229 g)
Unit Type Of Package 3	S04
Number Of Units In Package 3	1600
Package 3 Height	11.81 in (30 cm)
Package 3 Width	15.75 in (40 cm)
Package 3 Length	23.62 in (60 cm)
Package 3 Weight	17.95 lb(US) (8.142 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Halogen Free Plastic Parts Product	

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)