



Spacial SF-E rear cable guide support - steel - zinc coated - 150 mm

NSYRCSUP15

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 88.08 USD

Main

Range	Spacial
Accessory / Separate Part Category	Cabling accessory
Product Or Component Type	Cable guide
Application	Electronic application Multi-purpose
Mounting Location	Rear of swing rack
Range Compatibility	Spacial Spacial SF Spacial Spacial SM
Device Composition	fixing elements 1 crossbar 2 cable guide support
Quantity Per Set	Set of 1

Complementary

Material	steel
Surface Finish	Zinc coated
Fixing Mode	Clip-on - 19" rack profile
Adjustment	Adjustable in height every 44.45 mm
Height	1.18 in (30 mm)
Width	Nominal 23.62 in (600 mm)
Depth	5.91 in (150 mm)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480067112
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Height	1.38 in (3.5 cm)
Package 1 Width	3.94 in (10.0 cm)
Package 1 Length	22.44 in (57.0 cm)
Package 1 Weight	19.68 oz (558.0 g)
Unit Type Of Package 2	PAM
Number Of Units In Package 2	500
Package 2 Height	39.37 in (100.0 cm)
Package 2 Width	39.37 in (100.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	639.34 lb(US) (290.0 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations