Product data sheet

Specifications





Set of 4 step slides made of treated steel, D200mm

NSYSDCR200

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 49.74 USD

Main

Category	Mounting accessory
Product Or Component Type	Step slide
Range Compatibility	Spacial Spacial CRN
	Spacial Spacial S3D
	Spacial Spacial S3CM
	Spacial Spacial S3X
Application	Multi-purpose
Nominal Dimensions Of The Housing	-
Mounting Location	Sides of enclosure
Device Composition	4 sliding rails
	4 sliding support
	fixing elements
Quantity Per Set	Set of 1
Material	galvanised steel

Complementary

Fixing Mode	By fixing element On backstuds (welded in the enclosure)
Adjustment	In depth of the plate or other accessories in steps of 12.5 mm
Depth	Nominal 7.87 in (200 mm)
Net Weight	1.10 lb(US) (0.5 kg)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480184260
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.36 in (6.0 cm)
Package 1 Width	5.31 in (13.5 cm)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 1 Length

6.69 in (17.0 cm)

Package 1 Weight

17.64 oz (500.0 g)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations