

# Product data sheet

Specifications



## Spacial SF/SM door cross rails - nominal width: 500 mm



NSYSDCR5

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 54.45 USD

### Main

Range	Spacial
Product Or Component Type	Door cross rail
Application	Multi-purpose
Nominal Dimensions Of The Housing	-
Mounting Location	On door reinforcement frame
Mounting Support	Direct mounting
Range Compatibility	Spacial SF, SM, SFX and SMX enclosures
Device Composition	2 x cross rail 1 x bag of fixing
Quantity Per Set	Set of 1

### Complementary

Material	Body of the rail galvanised steel
Surface Finish	Zinc coated
Adjustment	Adjustable in height every 25 mm on door reinforcement frame
Height	Nominal 0.71 in (18 mm)
Width	Nominal 19.69 in (500 mm)
Depth	0.73 in (18.6 mm)
Thickness	0.08 in (2 mm)

### Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606485131351
Returnability	No
Country Of Origin	ES

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.38 in (3.5 cm)
Package 1 Width	1.97 in (5.0 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	14.96 in (38.0 cm)
Package 1 Weight	18.24 oz (517.0 g)

## Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations