

Product data sheet

Specifications



Spacial SF bottom and top frame - 1600x400 mm

NSYSFC164

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 237.78 USD

Main

Range	PanelSeT
Accessory / Separate Part Category	Enclosure accessory
Application	Multi-purpose
Product Or Component Type	Framework kit
For Enclosure Nominal Dimensions	- H: 78.74 in (2000 mm) W: 62.99 in (1600 mm) D: 15.75 in (400 mm)
Mounting Location	Top of vertical uprights Bottom of vertical uprights
Range Compatibility	PanelSeT rear panel PanelSeT side panel PanelSeT vertical upright
Device Composition	1 bottom frame 1 roof 1 top frame
Quantity Per Set	Set of 1

Complementary

Material	steel
Color	Gray RAL 7035)
Surface Finish	Epoxy-polyester powder
Fixing Mode	By screws - each corner of enclosure
Width	62.99 in (1600 mm)
Depth	External 15.75 in (400 mm)

Ordering and shipping details

Category	US10ES180035
Discount Schedule	0ES1
Gtin	3606485119106
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.12 in (13.0 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	16.14 in (41.0 cm)
Package 1 Length	64.57 in (164.0 cm)
Package 1 Weight	70.55 lb(US) (32.0 kg)
Unit Type Of Package 2	P2M
Number Of Units In Package 2	10
Package 2 Height	33.46 in (85.0 cm)
Package 2 Width	78.74 in (200.0 cm)
Package 2 Length	47.24 in (120.0 cm)
Package 2 Weight	756.19 lb(US) (343.0 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.