Product data sheet

Specifications





mm

NSYSFD185

! To be discontinued on: Sep 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

Spacial SF plain door - 1800x500

Price*: 473.85 USD

Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Door
Application	Multi-purpose
For Enclosure Nominal Dimensions	-
Mounting Location	Side
Range Compatibility	Spacial Spacial SF
Device Composition	1 door 1 lock with handle and 5 mm double bar insert 1 locking bar system 4 points 1 reinforcement frame 4 hinges 4 locking bar catches
Quantity Per Set	Set of 1

Complementary

Material	sheet steel
Color	Gray RAL 7035)
Surface Finish	Epoxy-polyester powder
Lock Type	Lock 5 mm double bar
Number Of Locks	1
Door Type	External plain
Door Opening Side	Reversible 120 °)
Maximum Load	60 kg/m²
Height	Nominal 70.87 in (1800 mm)
Width	Nominal 19.69 in (500 mm)

Ordering and shipping details

Category	US10ES180035
Discount Schedule	0ES1
Gtin	3606485131634
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.17 in (5.5 cm)
Package 1 Width	18.70 in (47.5 cm)
Package 1 Length	74.21 in (188.5 cm)
Package 1 Weight	44.09 lb(US) (20.0 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations