Product data sheet





Cable passage IP65 w/o connectors, 17 entries.

NSYTSA2417SE

! Discontinued on: Dec 31, 2022

! To be end-of-service on: Dec 31, 2024



Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	Spacial
Product Or Component Type	Quick entrance plate
Accessory / Separate Part Category	Cable management accessory
Device Application	Multi-purpose
Range Compatibility	Spacial Spacial S3D compact enclosure Spacial Spacial CRN compact enclosure Spacial Spacial S3CM control enclosure Spacial Spacial SBM industrial box Thalassa Thalassa PLA suitable enclosure Thalassa Thalassa PHD suitable enclosure Thalassa Thalassa PLM compact enclosure Thalassa Thalassa PLM compact enclosure Spacial Spacial S3HD compact enclosure
Device Composition	1 fixing elements 1 plate
Quantity Per Set	Set of 1

Complementary

Mounting Support	Cable gland plate Body of enclosure
Material	polyamide
Fixing Mode	By fixing element
Total Cable Entry Number	17
Cable Entry Number	17 x 0.200.36 in (59.2 mm)
Height	Real 0.55 in (14 mm)
Width	Real 5.75 in (146 mm) Cut-out 4.41 in (112 mm) Fixing center 5.12 in (130 mm)
Depth	Real 2.28 in (58 mm) Cut-out 1.42 in (36 mm) Fixing centre 1.26 in (32 mm)
Net Weight	0.36 lb(US) (0.164 kg)

Environment

Ip Degree Of Protection IP65

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Life Is On Schneider Apr 19, 2024



Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480168239
Returnability	No
Country Of Origin	FR

Packing Units

r adming dimes	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.38 in (3.5 cm)
Package 1 Width	3.15 in (8 cm)
Package 1 Length	6.50 in (16.5 cm)
Package 1 Weight	5.78 oz (164 g)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	7.87 in (20 cm)
Package 2 Width	7.87 in (20 cm)
Package 2 Length	11.81 in (30 cm)
Package 2 Weight	3.71 lb(US) (1.684 kg)
Unit Type Of Package 3	PAM
Number Of Units In Package 3	400
Package 3 Height	19.69 in (50 cm)
Package 3 Width	39.37 in (100 cm)
Package 3 Length	47.24 in (120 cm)
Package 3 Weight	187.39 lb(US) (85 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations