Product data sheet

Specifications





Lifting brackets, PanelSeT SFN, Spacial SF, set of 4

NSYSFELB

Product availability: Stock - Normally stocked in distribution facility

Price*: 46.94 USD

Main

Area	Spacial
Category	Lifting accessory
Product Or Component Type	Lifting bracket
Application	Multi-purpose
Mounting Location	Enclosure top
Mounting Support	Directly in the axis of the uprights
Range Compatibility	Spacial Spacial SF Spacial Spacial SFHD Spacial Spacial SFM
Device Composition	4 bracket fixing elements
Quantity Per Set	Set of 1

Complementary

Material	steel
Surface Finish	Zinc coated
Fixing Mode	By screws M12
Permanent Permissible Load	1102.31 lb(US) (500 kg)
Height	2.36 in (60 mm)
Width	3.94 in (100 mm)
Depth	1.93 in (49 mm)
Diameter	1.26 in (32 mm)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606485131559
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount �� check with your local distributor or retailer for actual price.

Package 1 Height	2.95 in (7.500 cm)
Package 1 Width	3.54 in (9.000 cm)
Package 1 Length	5.91 in (15.000 cm)
Package 1 Weight	4.25 lb(US) (1.930 kg)
Unit Type Of Package 2	S02
Number Of Units In Package 2	6
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	26.10 lb(US) (11.840 kg)
Unit Type Of Package 3	P12
Number Of Units In Package 3	96
Package 3 Height	17.72 in (45.000 cm)
Package 3 Width	31.50 in (80.000 cm)
Package 3 Length	47.24 in (120.000 cm)
Package 3 Weight	444.10 lb(US) (201.440 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations