Product data sheet

Specification





Spacial CRN Insulated 360x163mm. RAL7035.

NSYTSACRNC

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 34.74 USD

Main

Range	Spacial
Product Or Component Type	Cable gland plate
Accessory / Separate Part Category	Cable management accessory
Application	Multi-purpose
Range Compatibility	Spacial Spacial CRN
Mounting Location	Enclosure bottom
Cable Gland Type	Knock-out
Cable Entry	2 knock-outs Pg 11 2 knock-outs Pg 21/11 4 knock-outs Pg 13.5 5 knock-outs Pg 16 4 knock-outs Pg 29/16 2 knock-outs Pg 36/29
Device Composition	fixing elements 1 plate 1 separated seal
Quantity Per Set	Set of 1
Material	Seal polyethylene (PE) foam Plate ABS with 30 % fibre glass

Complementary

•	•
Color	Plate Gray RAL 7035)
Number Of Cut-Out	Pre-marked hole
Height	6.42 in (163 mm) 0.59 in (15 mm)
Width	14.17 in (360 mm) Real 14.96 in (380 mm)
Depth	6.42 in (163 mm)
Net Weight	0.60 lb(US) (0.272 kg)
Thickness	0.04 in (1 mm)

Ordering and shipping details

Category	US10ES180036
Discount Schedule	0ES1
Gtin	3606480211546
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin ES

Packing Units

9	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.59 in (1.500 cm)
Package 1 Width	6.50 in (16.500 cm)
Package 1 Length	14.17 in (36.000 cm)
Package 1 Weight	9.81 oz (278.000 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	25
Package 2 Height	11.81 in (30 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	16.25 lb(US) (7.370 kg)
Unit Type Of Package 3	P12
Number Of Units In Package 3	200
Package 3 Height	17.72 in (45.000 cm)
Package 3 Width	31.50 in (80.000 cm)
Package 3 Length	47.24 in (120.000 cm)
Package 3 Weight	156.44 lb(US) (70.960 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations